

Garant**Arbor, HSK-A 100, ABS® Ø d: 50mm****Order data**

Order number	238520 50
GTIN	4067263111047
Item class	29W

Description**Version:**

- Arbor balanced to Q 6.3 at 10,000 rpm.
- With through coolant feed.

Standard:**DIN 69893****Note:**

Further arbors with ABS® connection on request.

Technical description

Overhang A	80 mm
Projection length L ₁	51 mm
ABS® Ø d	50 mm
Adapter	HSK-A 100
Shank	ABS
Arbor standard	DIN 69893
Through-coolant	yes
External Ø d ₁	100 mm

Type of product

ABS mounting