

Mahr**Digital height gauge and marking-out system with data output, Marking height: 980mm****Order data**

Order number	445000 980
GTIN	4059192066789
Item class	43B

Description**Version:**

High contrast, 12 mm high LCD display. Stable ergonomic base with hardened and lapped surface for smooth movement without jolts. Beam and slide of hardened stainless steel. Large handwheel for positioning and measuring. Additional **fine adjustment and locking screw**.

Supplied with:

1 battery No. 081560 size CR2032, 1 carbide tipped scriber No. 445002.

Optional extras:

Holder for lever indicators No. 445004. Data cable No. 498940.

Technical description

Scale divisions	0.01 mm
Error limit	0.06 mm
Base length	220 mm
Scale divisions	0.0005 in
Power supply	Battery-powered
Column cross section	35×15 mm

Article no of the battery / rechargeable battery fitted	081560 CR2032
Base width	120 mm
Number of batteries contained	1
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	RS232C interface
Interface	Digimatic interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device