

**KOMET® Unisix® indexable insert, BK72, Designation type W29: 50-010****Order data**

Order number	236830 50-010
GTIN	4047109036345
Item class	24T

Description**Suitable for :**

No. 236685; 236686

Note:**The standard application values refer to the KUB Trigon®.**

Type: ST1400

ISO code indexable insert: WOEX 100504

Feed f in steel < 900 N/mm²: 0.2 mm/rev.**Technical description**

Designation	50-010
Feed f in steel < 900 N/mm ²	0.2 mm/rev.
ISO code indexable insert	WOEX 100504
Grade	BK72
Type	ST1400
Tool material	Carbide
Type of product	Indexable insert for drilling

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	300 m/min	P
Steel < 750 N/mm ²	suitable	250 m/min	P
Steel < 900 N/mm ²	suitable	200 m/min	P
Steel < 1100 N/mm ²	suitable	160 m/min	P
Steel < 1400 N/mm ²	suitable	130 m/min	P
GG(G)	suitable only under restricted conditions	200 m/min	K
wet maximum	suitable		