

HEDI

LED floodlight, 230 V, Power consumption: 35W



Order data

Order number	081268 35
GTIN	4003644005604
Item class	08B

Description

Version:

Non-shadowing and non-dazzle version with wide spread of light.

Robust work lamp with rubberised side parts and five different inclination angles depending on the positioning (90°, 35°, 25°, 15°, 0°). Integral carrying handle, on/off switch at the back.

Approved for continuous use and on building sites/installation sites to BGI 608.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

Illumination: 3850 lm

Overall length: 273 mm

Overall width: 256 mm

Overall height: 163 mm

Connection cable length: 3 m

Weight: 2300 g

Technical description

Beam dispersion angle adjustable	90 °
Beam dispersion angle adjustable	35 °
Beam dispersion angle adjustable	25 °
Beam dispersion angle adjustable	15 °
Beam dispersion angle adjustable	0 °
Power consumption	35 W
Weight	2300 g
Illumination	3850 lm
Power supply	Mains-powered
IP Index of Protection	IP 54
Nominal voltage	230 V
Overall length	273 mm
Overall width	256 mm
Overall height	163 mm
Connection cable length	3 m
ATEX zone	no
Product name attribute	230 V
Type of product	Area light