


KOMET® Unisix® indexable insert, BK62, Designation type W29: 18-010

Order data

Order number	236780 18-010
GTIN	4047109058613
Item class	24T

Description
Suitable for :

No. 236630; 236635; 236650; 236685; 236686

Note:

The standard application values refer to the KUB Trigon®.

Type: GG(G)

ISO code indexable insert: WOEX 040304

Feed f in steel < 900 N/mm²: 0.13 mm/rev.

Technical description

Designation	18-010
Feed f in steel < 900 N/mm ²	0.13 mm/rev.
ISO code indexable insert	WOEX 040304
Grade	BK62
Type	GG(G)
Tool material	Carbide
Type of product	Indexable insert for drilling

User data

	Suitability	V_c	ISO code
GG(G)	suitable	200 m/min	K
wet maximum	suitable		