


**KOMET® Unisix® indexable insert, BK62, Designation type W29: 34-010**

**Order data**

Order number	236780 34-010
GTIN	4047109058996
Item class	24T

**Description**
**Suitable for :**

No. 236650; 236660; 236685; 236686

**Note:**

**The standard application values refer to the KUB Trigon®.**

Type: GG(G)

ISO code indexable insert: WOEX 06T304

Feed f in steel < 900 N/mm<sup>2</sup>: 0.15 mm/rev.

**Technical description**

Designation	34-010
Feed f in steel < 900 N/mm <sup>2</sup>	0.15 mm/rev.
ISO code indexable insert	WOEX 06T304
Grade	BK62
Type	GG(G)
Tool material	Carbide
Type of product	Indexable insert for drilling

---

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
GG(G)	suitable	200 m/min	K
wet maximum	suitable		