

**KOMET® Unisix® indexable insert, BK62, Designation type W29: 50-010****Order data**

| | |
|--------------|---------------|
| Order number | 236780 50-010 |
| GTIN | 4047109059566 |
| Item class | 24T |

Description**Suitable for :**

No. 236685; 236686

Note:**The standard application values refer to the KUB Trigon®.**

Type: GG(G)

ISO code indexable insert: WOEX 100504

Feed f in steel < 900 N/mm²: 0.2 mm/rev.**Technical description**

| | |
|---|-------------------------------|
| Designation | 50-010 |
| Feed f in steel < 900 N/mm ² | 0.2 mm/rev. |
| ISO code indexable insert | WOEX 100504 |
| Grade | BK62 |
| Type | GG(G) |
| Tool material | Carbide |
| Type of product | Indexable insert for drilling |

User data

| | Suitability | V_c | ISO code |
|-------------|--------------------|----------------------|-----------------|
| GG(G) | suitable | 200 m/min | K |
| wet maximum | suitable | | |