

Vario plus Eco toolholder, left-hand, Shank mounting type: HSK63



Order data

Order number	274531 HSK63
GTIN	4067263112426
Item class	21U

Description

Version:

Optimised system stability thanks to multiple screw clamping and form fit.

Suitable for:

Vario plus Eco blade carrier.

Supplied with:

Including assembly screws.

Technical description

Overhang dimension A	105 mm
Shank mounting type	HSK63
h_1	19 mm
Clamping strip	279928 7
f_1	7 mm
L_2	35 mm
Clamping screw	279815 24
h_2	23 mm
Assembly bolt	279815 9
f_2	15 mm

L ₁	79 mm
Through-coolant	yes
h ₃	54 mm
Series	Vario plus Eco
Application type	left-hand
Type of product	Toolholder for parting-off tools

Accessories

Clamping screw, Type: 24	279815 24
Clamping screw, Type: 9	279815 9
Clamping rail, Type: 7	279928 7