

Garant
Vario Plus Eco Y tool holder, right-hand, Groove width w: 3mm

Order data

Order number	274540 3
GTIN	4067263112440
Item class	21U

Description
Version:

For parting off shafts with a maximum diameter of 90 mm.

Suitable for:

Vario plus Eco toolholder No. 274530; 274500; 274503.

Attention:

Without clamping screws (these are supplied with the toolholders).

Technical description

axial grooving possible	no
Groove width w	3 mm
maximum cutting depth t_{\max}	45 mm
Series	Vario plus Eco
Clamping screw	279815 9
suitable indexable insert	273656 – 273749

Overall length L	90.8 mm
X	47 mm
Y	28 mm
Y1	2 mm
X1	9 mm
Application type	right-hand
Through-coolant	yes
Type of product	Cartridges

Accessories

Clamping screw Type 9	279815 9
-----------------------	----------