


DC.T 070204, Grade: CA6525

Order data

Order number	260382 CA6525
GTIN	4960664589234
Item class	25E

Description

DC.T 070204 CA6525 Grade: CA6525
 Chip breaker: MQ
 Tolerance: M
 Cutting depth a_p : 0.5 - 1.5 mm
 Feed f : 0.05 - 0.25 mm/rev.
 Cutting speed v_c main application: 50 - 140 m/min

Technical description

Corner radius	0.4 mm
Cutting conditions	slightly interrupted
Chip breaker	MQ
Cutting depth a_p	0.5 - 1.5 mm
Feed f	0.05 - 0.25 mm/rev.
Main application	M
Cutting speed v_c main application	50 - 140 m/min

Grade	CA6525
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCMT 070204
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning