



## Top jaw set, 3 pieces, soft, for chuck type: 125mm



### Order data

Order number	314425 125
GTIN	4067263113010
Item class	32R

### Description

**Version:**

**Precision milled** contact face, **not burnished.**

**Application:**

For fitting to hardened base jaws.

**Material:**

16 MnCr5

**Suitable for:**

**Three-jaw lathe chucks No. 310505; 310655; 310705.**

**Note:**

- **Jaws can generally be renewed in the chuck as long as the guide in the body is not worn out.**
- **Top, turning, and drilling jaws bought subsequently must be ground in the chuck for radial and axial run-out.**

### Technical description

Slot width D	7.96 mm
Height H	38 mm
for chuck type	125 mm
Length L	62 mm
Tenon length A	12.67 mm

## Data sheet

Bore spacing b	32 mm
suitable for colour code	HOLEX geared scroll chucks and jaws
Type of product	Gear scroll chuck jaws