



Pneumatic straight die grinder, Type: SPM60R



Order data

Order number	079440 SPM60R
GTIN	
Item class	03P

Description

Version:

ATA – Pneumatic straight die grinder **with 3 mm collets** for fine milling, grinding and engraving. **Integral pre-filter.** 85 W straight die grinder with high operating comfort with a maximum speed of 60000 rpm.

- **Slim design for restricted working.**
- **Removable collet guard.**

Technical description

maximum air consumption	230 l/min
maximum speed	60000 min ⁻¹
Weight	0.17 kg
maximum vibration to EN	< 2,5 m/s ²
Compressed air connection	1/4 in
Length	140 mm
Connection thread	BSP
Operating noise	68 dB(A)
Output power	85 W
Collet Ø	3 mm
Type of product	Straight die grinder

