



## Pneumatic straight die grinder, Type: SPT100R



### Order data

Order number	079440 SPT100R
GTIN	5390145244663
Item class	03R

### Description

#### Version:

ATA – Pneumatic straight die grinder **with 3 mm collets** for fine milling, grinding and engraving. **Integral pre-filter.** 63 W straight die grinder with unique motor design without wearing parts in the motor with a long service life and a maximum speed of 100000 rpm.

#### Application:

**Use only oil-free compressed air. Do not add oil!**

### Technical description

Weight	0.15 kg
maximum speed	100000 min <sup>-1</sup>
Collet Ø	3 mm
Length	135 mm
Compressed air connection	1/4 in
maximum air consumption	170 l/min
maximum vibration to EN	< 2,5 m/s <sup>2</sup>
Operating noise	70 dB(A)
Connection thread	BSP
Output power	63 W
Type of product	Straight die grinder

