



Pneumatic straight die grinder, Type: SPT80R



Order data

Order number	079440 SPT80R
GTIN	5390145244601
Item class	03R

Description

Version:

ATA – Pneumatic straight die grinder **with 3 mm collets** for fine milling, grinding and engraving. **Integral pre-filter.** 63 W straight die grinder with unique motor design without wearing parts in the motor with a long service life and a maximum speed of 800000 rpm.

Application:

Use only oil-free compressed air. Do not add oil!

Technical description

Connection thread	BSP
maximum air consumption	170 l/min
Collet Ø	3 mm
Compressed air connection	1/4 in
maximum vibration to EN	< 2,5 m/s ²
Output power	63 W
Weight	0.15 kg
maximum speed	80000 min ⁻¹
Operating noise	68 dB(A)
Length	135 mm
Type of product	Straight die grinder

