



Pneumatic straight die grinder, Type: S25



Order data

Order number	079442 S25
GTIN	5390145244687
Item class	03R

Description

Version:

ATA – Pneumatic straight die grinder **with 6 mm collet**. Ergonomic straight die grinder for light to medium applications with one-handed operation.

- **Push-pull lever for continuous use.**
- **Excellent weight/performance ratio.**

Technical description

Output power	190 W
Length	164 mm
Connection thread	BSP
Weight	0.46 kg
maximum air consumption	450 l/min
Collet Ø	6 mm
maximum speed	25000 min ⁻¹
maximum vibration to EN	3.14 m/s ²
Operating noise	68 dB(A)
Compressed air connection	1/4 in
Type of product	Straight die grinders

