



## Pneumatic straight die grinder, Type: SDM26LR



### Order data

Order number	079442 SDM26LR
GTIN	5390145244700
Item class	03R

### Description

#### Version:

ATA – Pneumatic straight die grinder **with 6 mm collet**. Straight die grinder for light to medium applications with high user comfort and one-handed operation.

- **Speed control.**
- **Excellent weight/performance ratio.**

### Technical description

Length	154 mm
Collet Ø	6 mm
Output power	300 W
Connection thread	BSP
maximum air consumption	570 l/min
Compressed air connection	1/4 in
maximum speed	25000 min <sup>-1</sup>
maximum vibration to EN	3.14 m/s <sup>2</sup>
Operating noise	72 dB(A)
Weight	0.52 kg
Type of product	Straight die grinders

