



Pneumatic straight die grinder, Type: SMX16LR



Order data

| | |
|--------------|----------------|
| Order number | 079442 SMX16LR |
| GTIN | 5390145244830 |
| Item class | 03R |

Description

Version:

ATA – Pneumatic straight die grinder **with 6 mm collet**. Extended and ergonomic straight die grinder with two-handed operation.

- **Speed control.**
- **Smooth start-up.**

Technical description

| | |
|---------------------------|-------------------------|
| maximum air consumption | 620 l/min |
| Operating noise | 75 dB(A) |
| maximum speed | 16000 min ⁻¹ |
| Output power | 820 W |
| Connection thread | BSP |
| Weight | 1.3 kg |
| maximum vibration to EN | 3.19 m/s ² |
| Length | 345 mm |
| Collet Ø | 6 mm |
| Compressed air connection | 1/4 in |
| Type of product | Straight die grinders |

