



## Pneumatic straight die grinder, Type: SM25LR



### Order data

Order number	079442 SM25LR
GTIN	5390145244724
Item class	03R

### Description

#### Version:

ATA – Pneumatic straight die grinder **with 6 mm collet**. Powerful straight die grinder for the most demanding applications with high user comfort.

- **Speed control.**
- **Smooth start-up.**

### Technical description

Weight	0.75 kg
Length	213 mm
Connection thread	BSP
maximum vibration to EN	3.21 m/s <sup>2</sup>
Compressed air connection	1/4 in
maximum speed	25000 min <sup>-1</sup>
maximum air consumption	620 l/min
Output power	820 W
Collet Ø	6 mm
Operating noise	72 dB(A)
Type of product	Straight die grinders

