



## Pneumatic straight die grinder, Type: SMD25LR



### Order data

Order number	079442 SMD25LR
GTIN	5390145244847
Item class	03R

### Description

#### Version:

ATA – Pneumatic straight die grinder **with 6 mm collet**. Ergonomic straight die grinder with unique vibration damping system.

- **Smooth start-up.**

### Technical description

Connection thread	BSP
Length	208 mm
maximum vibration to EN	2.27 m/s <sup>2</sup>
Collet Ø	6 mm
maximum air consumption	620 l/min
Operating noise	77 dB(A)
Output power	820 W
Weight	0.8 kg
Compressed air connection	1/4 in
maximum speed	25000 min <sup>-1</sup>
Type of product	Straight die grinders

