



Pneumatic small angle grinder, Type: RAM20LR



Order data

Order number	079316 RAM20LR
GTIN	5390145244502
Item class	03R

Description

Version:

Compact angle grinder with ergonomic design and narrow head for easy access in confined spaces. Compact angle grinder with ergonomic design and narrow head for easy access in confined spaces. For Roloc® mini-grinding discs Ø 50/75 mm.

Technical description

maximum air consumption	1207 l/min
Compressed air connection	1/4 in
maximum vibration to EN	2.58 m/s ²
maximum disc Ø	75 mm
maximum speed	20000 min ⁻¹
Weight	0.6 kg
Operating noise	74 dB(A)
Output power	300 W
Connection thread	BSP
recommended hose size (internal Ø)	8 mm

Type of product

Angle grinder