



Push-out collet, round, to DIN 6343, 185 E, Clamping \varnothing : 27mm



Order data

| | |
|--------------|---------------|
| Order number | 329565 27 |
| GTIN | 4067263115755 |
| Item class | 32Z |

Description

Version:

Collets, **round profile in 1 mm increments. Please specify required clamping \varnothing with order.**

Standard:

DIN 6343

Accuracy:

Concentricity tolerances: D = 1 to 10 mm = 0.02 mm D = 10 to 30 mm = 0.03 mm D = 30 to 60 mm = 0.04 mm

Note:

Other diameters and profiles (e.g. square or hexagon) **on request!**

Profile \varnothing 4.0 – 8.0 mm smooth. From \varnothing 9.0 mm with transverse serrations.

Technical description

| | |
|------------------|------------|
| A | 73 mm |
| Angle α | 20 degrees |
| K | 84 mm |
| Overall length L | 110 mm |
| F | 66 mm |
| Type | 185 E |

Type of product

Collet