

Garant**DC.T 11T302, Grade: HB7310**

Order data

Order number	260458 HB7310
GTIN	4045197669568
Item class	21G

Description

DC.T 11T302 HB7310 Grade: HB7310
Chip breaker: AM
Tolerance: G
Cutting depth a_p : 0.1 - 4 mm
Feed f : 0.05 - 0.5 mm/rev.
Cutting speed v_c main application: 350 - 600 m/min

Technical description

Feed f	0.05 - 0.5 mm/rev.
Cutting speed v_c main application	350 - 600 m/min
Cutting depth a_p	0.1 - 4 mm
Cutting conditions	continuous
Chip breaker	AM
Corner radius	0.2 mm

Main application	N
Grade	HB7310
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DCGT 11T302
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning