

Garant**Electrician's screwdriver for PlusMinus screws, with 2-component Haptoprene handle, SLIM blade, VDE fully insulated, Profile size: 1****Order data**

Order number	668922 1
GTIN	4067263113331
Item class	61F

Description**Version:**

Handle and blade **fully insulated up to 1000 V to DIN EN IEC 60900 / VDE 0682-201**. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Ergonomically shaped **power grip** with easy-grip **Haptoprene** surface and an impact-resistant plastic core. The special surface structure allows transmission of high torques, even with wet or oily hands. **Blade** of chrome vanadium steel. Surface nickel-plated and chrome-plated, black tip. With **SLIM blade** = reduced blade/and insulation diameter for deep-set screw and spring elements (**insulation Ø = blade Ø**).

Application:

For use at voltages up to 1000 V.

The screwdriver drive tip fits perfectly into the **PlusMinus screws (combination Pozidriv / slot-head)**, which are primarily used in electrical installation components.

Technical description

Blade length	80 mm
overall length	180 mm
Profile Pozidriv – slot head	1 – 0.7×4.5
Profile size	1
Standard	DIN EN IEC 60900 / VDE 0682-201

Drive profile	Combination profile screwdriver Pozidriv/slot-head
Type of product	Screwdriver