

Garant

Electrician's screwdriver for PlusMinus screws, with 2-component Haptoprene handle, SLIM blade, fully insulated, Profile size: 1



Order data

| | |
|--------------|---------------|
| Order number | 668922 1 |
| GTIN | 4067263113331 |
| Item class | 61F |

Description

Version:

Handle and blade **fully insulated up to 1000 V to DIN EN IEC 60900 / VDE 0682-201**. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Ergonomically shaped **power grip** with easy-grip **Haptoprene** surface and an impact-resistant plastic core. The special surface structure allows transmission of high torques, even with wet or oily hands. **Blade** of chrome vanadium steel. Surface nickel-plated and chrome-plated, black tip. With **SLIM blade** = reduced blade/and insulation diameter for deep-set screw and spring elements (**insulation \varnothing = blade \varnothing**).

Application:

For use at voltages up to 1000 V.

The screwdriver drive tip fits perfectly into the **PlusMinus screws (combination Pozidriv / slot-head)**, which are primarily used in electrical installation components.

Technical description

| | |
|------------------------------|---------------------------------|
| Blade length | 80 mm |
| overall length | 180 mm |
| Profile Pozidriv – slot head | 1 – 0.7×4.5 |
| Profile size | 1 |
| Standard | DIN EN IEC 60900 / VDE 0682-201 |

| | |
|-----------------|---|
| Drive profile | Combination profile screwdriver Pozidriv/slot-head |
| Type of product | Screwdriver |