



Precision Circlip pliers set for internal and external circlips, Number of pliers: 8



Order data

Order number	700156 8
GTIN	
Item class	73F

Description

Version:

Forged grip and joint, precision made tips of special steel, special precision profile, pressed into the body. Pliers black, head ground, plastic coated handles.

Joint for external ring pliers with **integral opening spring**.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Standard:

DIN 5256 C und D – für Innensicherungsringe.

DIN 5254 A und B – für Außensicherungsringe.

Supplied with:

1 each circlip pliers No. 719790 size J1; J2; J11; J21.

1 each circlip pliers No. 719890 size A1; A2; A11; A21.

Note:

For set with case see No. 700155 size 8

Technical description

Tip Ø for internal circlip pliers	1.25; 1.8 mm
-----------------------------------	--------------

for external circlip Ø	10 – 25; 19 – 60 mm
for internal circlip Ø	12 – 25; 19 – 60 mm
Storage in	Plastic case
maximum overall length of external circlip pliers	130; 140; 175; 185; mm
Number of pliers	8
Use of circlip pliers	Outer ring, angled
Use of circlip pliers	Inner ring, angled
Use of circlip pliers	Inner ring, straight
Use of circlip pliers	Outer ring, straight
Tip Ø for external circlip pliers	1.25; 1.8 mm
maximum overall length of internal circlip pliers	130; 140; 170; 180; mm
Standard	DIN 5254 A and B
Standard	DIN 5256 C and D
Type of product	Retaining ring pliers

Accessories

Precision circlip pliers Type J11	719790 J11
Precision circlip pliers Type J21	719790 J21
Precision circlip pliers Type J2	719790 J2
Precision circlip pliers Type A11	719890 A11
Precision circlip pliers Type A2	719890 A2
Precision circlip pliers Type A1	719890 A1
Precision circlip pliers Type A21	719890 A21
Precision circlip pliers Type J1	719790 J1