



Pair of gloves Cut D, Glove size: 10



Order data

Order number	094661 10
GTIN	4067263116646
Item class	02H

Description

Version:

Gloves with new fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

HOLEX Cut D. Cut-resistant gloves with cut resistance level D and **18-gauge knit** for precision activities with high cut hazards.

Version of the advertising text:

Gloves with new DYTEC® fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

18-gauge knit for precision activities with moderate cutting hazards.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Knitted technology	18G
Clothing standard	Oeko-Tex Standard 100
EN 388	4342D
Backing material	Special yarn
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Precision
Colour	black / grey
Application	reusable
Cut protection class	D
Type of product	Cut-resistant gloves