

**Pair of gloves Cut E, Glove size: 7****Order data**

| | |
|--------------|---------------|
| Order number | 094662 7 |
| GTIN | 4067263116660 |
| Item class | 02H |

Description**Version:**

Gloves with new fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

HOLEX Cut E. Cut-resistant gloves with cut resistance level E and 15-gauge knit for variable activities with extreme cut hazards.

Version of the advertising text:

Gloves with new DYTEC® fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

15-gauge knit for variable activities with extreme cut hazards.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|----------------------|------------------------|
| Knitted technology | 15G |
| Clothing standard | Oeko-Tex Standard 100 |
| EN 388 | 4443E |
| Backing material | Special yarn |
| Coating | Nitrile foam |
| Coating variant | The palms of the hands |
| Application range | All-round |
| Colour | black / grey |
| Application | reusable |
| Cut protection class | E |
| Type of product | Cut-resistant gloves |