

HOLEX
Pair of gloves Cut F / A6, Glove size: 11

Order data

Order number	094663 11
GTIN	4067263116851
Item class	02H

Description
Version:

Gloves with new fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

HOLEX Cut F. Cut-resistant gloves with the highest EN-ISO cut resistance level F (equivalent to ANSI A6) and 13-gauge knit for heavy-duty activities with extreme cut hazards.

Version of the advertising text:

Gloves with new DYTEC® fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

Cut protection level F (equivalent to ANSI A6) for variable activities with extreme cut hazards.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Knitted technology	13G
Clothing standard	Oeko-Tex Standard 100
EN 388	4543F
Backing material	Special yarn
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey
Application	reusable
Cut protection class	F
Type of product	Cut-resistant gloves