



## LED cordless floodlight, Power consumption: 13



### Order data

Order number	081285 13
GTIN	5708997362013
Item class	08C

### Description

#### Version:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption.**
- **Certified for exterior use and for use in humid environments.**

**NOVA "For Life" cordless floodlight** with integrated carrying handle and 5-step dimmer function.

- **New, updated design with highly efficient multi-LEDs.**
- **New OPTILight function for optimised light output and superior duration.**
- **Compact and durable for demanding work environments.**

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Supplied with USB charging cable and plug-in power supply unit.

### Technical description

Power supply	Mains operated
--------------	----------------

## Data sheet

Overall length	163 mm
Overall height	163 mm
Illumination	200 - 2000 lm
Power consumption	13 W
Overall width	63 mm
Type of rechargeable battery	Lithium-ion
IP Index of Protection	IP 67