



## LED floodlight, 230 V, Power consumption: 43W



### Order data

Order number	081245 43
GTIN	5708997362037
Item class	08C

### Description

#### Version:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption.**
- **Certified for exterior use and for use in humid environments.**

**NOVA "For Life" LED floodlight** with integrated carrying handle and 5-step dimmer function.

- **New, updated design with highly efficient multi-LEDs.**
- **New OPTILight function for optimised light output and superior duration.**
- **Compact and durable for demanding work environments.**

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

### Technical description

Overall height	262 mm
Overall width	87 mm
Illumination	600 - 6000 lm
Connection cable length	5 m

IP Index of Protection	IP 67
Overall length	267 mm
Power supply	Mains-powered
Weight	2660 g
Product name attribute	230 V
Type of product	Floodlight