

“No Go” ring gauge, Type: G



Order data

Order number	484038 G
GTIN	4067263129905
Item class	48B

Description

Version:

Made of first class gauge steel, hardened, stress-relieved, ground and lapped. Rings with intermediate size and ISO fit, e.g. No. 484037 **5.56 h6** or numerical tolerance, e.g. No. 484037 **28 0.01 / -0.02**.

Application:

Smooth rings for gauging the external diameter.

Standard:

Nach **DIN 2254-A**.

Note:

State the exact nominal \varnothing with tolerance band (a-zc) and quality (6-13) or numeric tolerance (\pm) when ordering. Gauges for precision fit quality 5 and finer tolerances available on request.

Technical description

Quality	6
Quality	7
Quality	8
Quality	9

Quality	10
Quality	11
Quality	12
Quality	13
Standard	DIN 2254-A
Nominal size	32 - 39.999 mm
Material	Gauge steel
Tolerance zone	a
Tolerance zone	b
Tolerance zone	c
Tolerance zone	cd
Tolerance zone	d
Tolerance zone	e
Tolerance zone	ef
Tolerance zone	f
Tolerance zone	fg
Tolerance zone	g
Tolerance zone	h
Tolerance zone	j
Tolerance zone	js
Tolerance zone	k
Tolerance zone	m
Tolerance zone	n
Tolerance zone	p
Tolerance zone	r
Tolerance zone	s
Tolerance zone	t
Tolerance zone	u
Tolerance zone	v

Tolerance zone	x
Tolerance zone	y
Tolerance zone	z
Tolerance zone	za
Tolerance zone	zb
Tolerance zone	zc
Calibration	L7
Type of product	setting ring

Services

CalibrationSetting ring maximum \varnothing 50 mm	028400 50
DAkkS calibrationSetting ring maximum \varnothing 50 mm	028470 50