

## “Go” ring gauge, Type: B



### Order data

Order number	484037 B
GTIN	4067263128175
Item class	48B

### Description

#### Version:

Made of first class gauge steel, hardened, stress-relieved, ground and lapped. Rings with intermediate size and ISO fit, e.g. No. 484037 **5.56 h6** or numerical tolerance, e.g. No. 484037 **28 0.01 / -0.02**.

With wear allowance.

#### Application:

Smooth rings for gauging the external diameter.

#### Standard:

Nach **DIN 2250-G**.

#### Note:

State the exact nominal  $\varnothing$  with tolerance band (a-zc) and quality (6-13) or numeric tolerance ( $\pm$ ) when ordering. Gauges for precision fit quality 5 and finer tolerances available on request.

### Technical description

Nominal size	4 - 9.999 mm
Quality	6
Quality	7

Quality	8
Quality	9
Quality	10
Quality	11
Quality	12
Quality	13
Tolerance zone	a
Tolerance zone	b
Tolerance zone	c
Tolerance zone	cd
Tolerance zone	d
Tolerance zone	e
Tolerance zone	ef
Tolerance zone	f
Tolerance zone	fg
Tolerance zone	g
Tolerance zone	h
Tolerance zone	j
Tolerance zone	js
Tolerance zone	k
Tolerance zone	m
Tolerance zone	n
Tolerance zone	p
Tolerance zone	r
Tolerance zone	s
Tolerance zone	t
Tolerance zone	u
Tolerance zone	v
Tolerance zone	x

Tolerance zone	y
Tolerance zone	z
Tolerance zone	za
Tolerance zone	zb
Tolerance zone	zc
Material	Gauge steel
Standard	DIN 2250-G
Calibration	L7
Type of product	setting ring

## Services

CalibrationSetting ring maximum Ø 50 mm	028400 50
DAkkS calibrationSetting ring maximum Ø 50 mm	028470 50