

“No Go” ring gauge, Type: E



Order data

Order number	484038 E
GTIN	4067263129882
Item class	48B

Description

Version:

Made of first class gauge steel, hardened, stress-relieved, ground and lapped. Rings with intermediate size and ISO fit, e.g. No. 484037 **5.56 h6** or numerical tolerance, e.g. No. 484037 **28 0.01 / -0.02**.

Application:

Smooth rings for gauging the external diameter.

Standard:

Nach **DIN 2254-A**.

Note:

State the exact nominal \varnothing with tolerance band (a-zc) and quality (6-13) or numeric tolerance (\pm) when ordering. Gauges for precision fit quality 5 and finer tolerances available on request.

Technical description

Quality	6
Quality	7
Quality	8
Quality	9

Quality	10
Quality	11
Quality	12
Quality	13
Material	Gauge steel
Tolerance zone	a
Tolerance zone	b
Tolerance zone	c
Tolerance zone	cd
Tolerance zone	d
Tolerance zone	e
Tolerance zone	ef
Tolerance zone	f
Tolerance zone	fg
Tolerance zone	g
Tolerance zone	h
Tolerance zone	j
Tolerance zone	js
Tolerance zone	k
Tolerance zone	m
Tolerance zone	n
Tolerance zone	p
Tolerance zone	r
Tolerance zone	s
Tolerance zone	t
Tolerance zone	u
Tolerance zone	v
Tolerance zone	x
Tolerance zone	y

Tolerance zone	z
Tolerance zone	za
Tolerance zone	zb
Tolerance zone	zc
Standard	DIN 2254-A
Nominal size	20 - 24.999 mm
Calibration	L7
Type of product	setting ring

Services

CalibrationSetting ring maximum \varnothing 50 mm	028400 50
DAkkS calibrationSetting ring maximum \varnothing 50 mm	028470 50