

**DC.T 070204, Grade: CA510****Order data**

Order number	260382 CA510
GTIN	4960664697557
Item class	25E

Description

DC.T 070204 CA510 Grade: CA510

Chip breaker: HQ

Tolerance: M

Cutting depth a_p : 0.5 - 1.5 mm

Feed f : 0.05 - 0.25 mm/rev.

Cutting speed v_c main application: 140 - 450 m/min

Technical description

Feed f	0.05 - 0.25 mm/rev.
Cutting conditions	continuous
Cutting depth a_p	0.5 - 1.5 mm
Cutting speed v_c main application	140 - 450 m/min
Corner radius	0.4 mm
Chip breaker	HQ
Main application	P

Grade	CA510
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCMT 070204
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning