



Cordless angle grinder GWS, Type: GWS18-10SC



Order data

Order number	077120 GWS18-10SC
GTIN	3165140960878
Item class	03C

Description

Version:

Powerful **18 V cordless angle grinder**.

- **Same performance as a wired 1000 watt grinder thanks to brushless motor and ProCORE 18 V rechargeable battery.**
- **Drop Control, KickBack Control and Intelligent Brake System for maximum user protection and comfort.**
- **Bluetooth module for customisation via Toolbox app. User interface for active tool feedback and speed preselection.**

Supplied with:

Includes 2 pcs. ProCORE 18 V rechargeable battery, mounting flange, charger, quick clamping nut, 1 pc. Bluetooth Low Energy Module GCY 42 Professional, safety guard and L-BOXX.

Note:

See No. 073854 and No. 073866 for suitable spare batteries and chargers.

Technical description

maximum vibration to EN	6 m/s ²
Battery voltage	18 V
maximum disc Ø	125 mm
electronic speed pre-selection	yes

Interface	Bluetooth interface
Restart block	yes
Type of rechargeable battery	Lithium-ion
maximum speed	9000 min ⁻¹
Number of rechargeable batteries contained	0
Kick-back stop	yes
Overload protection	yes
Power supply	Mains operated
Packaging	Modular case (L-Boxx)
maximum cutting depth	34 mm
Manufacturer's designation	GWS 18V-10 SC
Dead man's circuit	no
Weight	2 kg
Soft start	no
Motor design	brushless
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Angle grinder