



## TubiX® pipe cutter with quick adjustment, for Ø to: 30mm



### Order data

Order number	818380 30
GTIN	4003773090038
Item class	86A

### Description

#### Version:

Lightweight and long-lasting metal housing of magnesium, with needle bearing guide rollers and cutter wheel. Manual deburrer can be retracted into the body. Supplied with spare cutter wheel.

#### Advantage:

Automatic stop and clamping on to the pipe by **QuickLock quick adjustment**.

- **Quick and precise positioning of the cutter wheel on different pipe diameters.**

#### Application:

General purpose for cutting **copper, aluminium, and thin-walled stainless steel pipes** (up to 2 mm wall thickness).

#### Spare part:

For spare cutter wheel with needle bearing and quick-change pivot pin, see No. 818385.

### Technical description

Manufacturer's designation	TubiX
Length	54 mm
Cutter wheel bore	7.8 mm
for pipe outer Ø	3 - 30 mm
Cutter wheel Ø	20 mm

## Data sheet

Cutter wheel width	6.2 mm
Width	55 mm
Height	26 mm
Type of product	Pipe cutters

## Accessories

Spare cutter wheel Type 1	818385 1
---------------------------	----------