

Vario plus Eco toolholder, left-hand, Shank mounting type: PSC63



Order data

Order number	274531 PSC63
GTIN	4067263112228
Item class	21U

Description

Version:

Optimised system stability thanks to multiple screw clamping and form fit.

Suitable for:

Vario plus Eco blade carrier.

Supplied with:

Including assembly screws.

Technical description

Overhang dimension A	105 mm
Shank mounting type	PSC63
h_2	23 mm
L_2	35 mm
f_1	7 mm
L_1	83 mm
h_1	19 mm
f_2	15 mm
Clamping screw	279815 24
Clamping strip	279928 7

Assembly bolt	279815 9
Through-coolant	yes
h ₃	54 mm
Series	Vario plus Eco
Application type	left-hand
Type of product	Toolholder for parting-off tools

Accessories

Clamping screw, Type: 24	279815 24
Clamping screw, Type: 9	279815 9
Clamping rail, Type: 7	279928 7