



TESA

**TWIN-T40 display unit, Type: T40****Order data**

Order number	405571 T40
GTIN	2050002081161
Item class	45A

**Description****Version:**

Display unit for measured values with easy-to-read 7-inch colour touch screen. Simultaneous display of 1 or 2 measurements possible via the 2 ports for inductive contact points or the two USB inputs. 4 display modes are available for optimum reading of the results. TESA contact points are recognised automatically. Dynamic measurement is ensured by picking up blank data of 4300/sec.

**Function:**

- **Basic formulas (+A, -A, +B, -B and combinations from A and B).**
- **Dynamic measurements (min., max., max.-min., average, etc.).**
- **Adjustable tolerances with OK/NOK display.**
- **Function for classification integrated (8 max.).**
- **Data output via RS232, USB or Bluetooth®.**

**Technical description**

IP Index of Protection	IP 65
Display	155 × 87
Length	112 mm
Measuring range	5000 µm
Height	119 mm

Width	190 mm
Power supply	Mains-powered
Reversible reading	mm / inch
Interface	TESA Link Connector TLC
Interface	Digimatic interface
Type of product	Display unit