

metabo**Construction site & workshop compressor, Type: 700/90D****Order data**

Order number	079842 700/90D
GTIN	4007430244833
Item class	03D

Description**Version:**

Powerful and robust compressor for demanding applications. Extremely high performance and long service life.

Technical description

AC supply voltage	380-415 V
Pressure vessel volume	90 l
Power consumption	4 kW
Manufacturer's designation	700/90D
maximum pressure (air)	11 bar
Width	520 mm
Height	1110 mm
maximum filling rate	520 l/min
Weight	119 kg

maximum suction rate	650 l/min
Length	1188 mm
Type of product	Compressor