



Pneumatic belt lisher, Type: 3260D12



Order data

Order number	079570 3260D12
GTIN	15451689629
Item class	03R

Description

Version:

Robust belt grinders for professional use.

- **360° swivelling grinding head**
- **Easy change of grinding media and contact arm**
- **Simple and robust design**

Linishing belt size 13×305 mm

Supplied with:

1 contact arm, linishing belt 13 × 305 mm.

Note:

You will find suitable linishing belts in Catalogue 55, Volume 2, pages 368–371.

Technical description

Compressed air connection	1/4 in
Weight	0.77 kg
Band length	305 mm
maximum air consumption	1020 l/min
maximum speed	26000 min ⁻¹
maximum vibration to EN	< 2.5 m/s ²
Manufacturer's designation	3260D12

Output power	300 W
Tape width	13 mm
Operating noise	81.5 dB(A)
Connection thread	NPT
Type of product	Belt grinders