



Pneumatic belt liner, Type: 3260D12K



Order data

Order number	079570 3260D12K
GTIN	15451689674
Item class	03R

Description

Version:

Robust belt grinders for professional use.

- **360° swivelling grinding head**
- **Easy change of grinding media and contact arm**
- **Simple and robust design**

Linishing belt size 3×305 mm, 8×305 mm, 13×305 mm, 16×305 mm

Supplied with:

4 contact arms, linishing belt 3×305 mm, 8×305 mm, 13×305 mm, 16×305 mm.

Note:

You will find suitable linishing belts in Catalogue 55, Volume 2, pages 368–371.

Technical description

Operating noise	81.5 dB(A)
Tape width	3, 13 16-19 mm
Connection thread	NPT
Weight	0.77 kg
maximum vibration to EN	< 2.5 m/s ²
maximum air consumption	1020 l/min

Band length	305 mm
Manufacturer's designation	3260D12K
Compressed air connection	1/4 in
Output power	300 W
maximum speed	26000 min ⁻¹
Type of product	Belt grinders

Accessories

Pneumatic belt linisher Type 3260D12	079570 3260D12
--------------------------------------	----------------