



## Pneumatic belt linisher, Type: 4200D24



### Order data

Order number	079570 4200D24
GTIN	15451689636
Item class	03R

### Description

#### Version:

Robust belt grinders for professional use.

- **360° swivelling grinding head**
- **Easy change of grinding media and contact arm**
- **Simple and robust design**

Linishing belt size 13×610 mm

#### Supplied with:

1 contact arm, linishing belt 13 × 610 mm.

#### Note:

You will find suitable linishing belts in Catalogue 55, Volume 2, pages 368–371.

### Technical description

Band length	610 mm
Output power	400 W
Operating noise	78 dB(A)
maximum air consumption	1260 l/min
Weight	1.39 kg
Tape width	13 mm
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Compressed air connection	1/4 in

Connection thread	NPT
maximum speed	20000 min <sup>-1</sup>
Manufacturer's designation	4200D24
Type of product	Belt grinders