



## Pneumatic belt linisher, Type: 4200H18K



### Order data

Order number	079570 4200H18K
GTIN	15451689667
Item class	03R

### Description

#### Version:

Robust belt grinders for professional use.

- **360° swivelling grinding head**
- **Easy change of grinding media and contact arm**
- **Simple and robust design**

Linishing belt size 3×457 mm, 13×457 mm, 16–19×457 mm

#### Supplied with:

4 contact arms, linishing belt 3×457 mm, 13×457 mm, 16×457 mm, 17×457 mm, 18×457 mm, 19×457 mm.

#### Note:

You will find suitable linishing belts in Catalogue 55, Volume 2, pages 368–371.

### Technical description

Compressed air connection	1/4 in
Weight	1.39 kg
Band length	457 mm
Output power	400 W
Operating noise	78 dB(A)

maximum vibration to EN	< 2.5 m/s <sup>2</sup>
maximum speed	20000 min <sup>-1</sup>
Connection thread	NPT
maximum air consumption	1260 l/min
Manufacturer's designation	4200H18K
Tape width	3, 13, 16-19 mm
Type of product	Belt grinders

---

## Accessories

Pneumatic belt liner Type 4200D24	079570 4200D24
-----------------------------------	----------------