

Inclined shelf extension rack, Width 1300 mm, Depth: 800mm**Order data**

Order number	990606 800
GTIN	4058255012749
Item class	96P

Description**Version:**

T-profile frames and storage shelves galvanised. Available with a **maximum load capacity of 150 kg per inclined shelf**. Storage shelf levels adjustable at 25-mm intervals. Quick assembly thanks to the simple plug-in design. Can be accessed from both sides. **Load per bay: 1300 kg**. Inclined shelf/Kanban racking that can be accessed from both sides, ideal for First-in-First-Out storage as the stored goods can slip to the front on the smooth galvanised shelves.

Assembled size of extension rack: 1306 mm.

Horizontal divider guides can be adjusted at 50 mm steps. The front lengthways bar is raised 15 mm and thus prevents goods falling off the shelves.

Description:**Extension size:**

Basic rack: Nominal length + 60mm

Extension rack: Nominal length + 6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Accepts plastic containers, clear-view containers, boxes and much more.

Supplied with:

7 inclined shelves each with 8 divider guides. 2 longitudinal bars. 2 lateral guides and 1 horizontal cover, including clip-on feet.

Note:

- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Rack depth	800 mm
Number of shelves	7
Depth	836 mm
Assembled size add-on rack width	1306 mm
Rack width	1300 mm
Width	1306 mm
Customer assembly	yes
maximum bay load	1300 kg
Rack height	2000 mm
Height	2000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	Galvanised
Product name attribute	Width 1300 mm
Type of product	Inclined shelf racking