

NOVUS[®]**Hand staple gun, Manufacturer's designation: J-29****Order data**

Order number	078407 J-29
GTIN	4009729082478
Item class	07E

Description**Version:**

User-friendly, ergonomic professional staple guns for precision driving of round-wire and flat staples and nails.

Durable professional staple gun with robust, low-recoil zinc die-cast housing. The re-strike function ensures that staples / nails of all types are driven flush.

- **Reload system in the base for quick and easy reloading.**
- **Distance stop for insertion of parallel rows of staples.**
- **Impact force control.**
- **Patented safety unlocking.**
- **Good access to restricted spaces.**
- **Staple supply viewing window.**

Technical description

Weight	1 kg
suitable type of staple	E, A, D, H, G
maximum staple insertion depth	16 mm

Version	Hand tacker
Manufacturer's designation	J-29
Type of product	Tacker