

NOVUS[®]**Cordless staple gun, Manufacturer's designation: J-551****Order data**

Order number	078409 J-551
GTIN	4009729079331
Item class	07E

Description**Version:**

User-friendly, ergonomic professional staple guns for precision driving of round-wire and flat staples and nails.

- **Reload system in the base for quick and easy reloading.**
- **Distance stop for insertion of parallel rows of staples.**
- **Impact force control.**
- **Patented safety unlocking.**
- **Good access to restricted spaces.**
- **Staple supply viewing window.**

Powerful, professional battery-powered tacker for perfect attachment of a wide variety of materials.

Supplied with:

Supplied with 1 pc. 18 V 2.0 Ah battery, charger, staples and transport case.

Note:

For suitable spare batteries see No. 073870.

Technical description

Power supply	Mains operated
Number of rechargeable batteries contained	1

Type of rechargeable battery	Lithium-ion
Weight	2.7 kg
suitable type of staple	D, G, E
maximum staple insertion depth	14 mm
Manufacturer's designation	J-214
Battery voltage	18 V
Battery capacity	2 Ah
Version	Battery-powered tacker
Type of product	Tacker

Accessories

Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery charger Type ASC145	073890 ASC145
Battery charger Type ASC55	073890 ASC55
Battery charger Type ASC55-8	073890 ASC55-8