

## Cordless hammer drill / driver, Type: GSB18V45



### Order data

Order number	070105 GSB18V45
GTIN	4059952635699
Item class	03B

### Description

#### Version:

**Bosch cordless hammer drill / driver** for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP) protects the battery against overheating and deep discharge.**
- **Electronic Motor Protection (EMP) protects the motor against overloading.**
- **Mechanical multi-stage torque cut-out.**
- **Handy belt clip (not 070104).**
- **Integral LED light, battery charge indicator.**
- **Quick-clamping drill chuck.**

Robust cordless screwdriver with powerful motor.

#### Supplied with:

Supplied with 2 pcs. 18V / 3.0 Ah Li-ion battery, charger and L-BOXX.

#### Note:

See from No. 073851 and 073866 for suitable replacement batteries and chargers.

### Technical description

maximum vibration to EN with hammer drill function	12.2 m/s <sup>2</sup>
----------------------------------------------------	-----------------------

maximum torque hard	45 Nm
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum twist drill size Ø in wood	35 mm
Manufacturer's designation	GSB 18V-45
maximum vibration to EN without hammer drill function	<2,5 m/s <sup>2</sup>
maximum speed 1st speed	0 - 500 min <sup>-1</sup>
maximum twist drill size Ø in steel	10 mm
Battery capacity	3 Ah
Type of rechargeable battery	Lithium-ion
Packaging	Modular case (L-Boxx)
maximum twist drill size Ø in concrete	10 mm
maximum torque soft	21 Nm
Power supply	Mains operated
Weight	1 kg
Motor design	Brushless motor
Number of rechargeable batteries contained	2
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 2nd speed	1900 min <sup>-1</sup>
typical application	Medium
Battery voltage	18 V
Type of product	limpact drill /screwdriver