

Cordless drill / driver, Type: GSR18V45



Order data

Order number	070243 GSR18V45
GTIN	4059952635675
Item class	03B

Description

Version:

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Outstanding available and comfortable handling due to **compact design. Motor brake** for precise working.

Supplied with:

Supplied with 2× Li-ion batteries, charger and L-BOXX.

Note:

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

Technical description

suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of rechargeable battery	Lithium-ion

Power supply	Mains operated
Number of rechargeable batteries contained	2
maximum torque soft	21 Nm
maximum twist drill size Ø in wood	35 mm
typical application	Medium
Battery voltage	18 V
maximum twist drill size Ø in steel	10 mm
Manufacturer's designation	GSR 18V-45
Speed range 1st speed	0 - 500 min ⁻¹
Packaging	Modular case (L-Boxx)
Quick-clamping chuck range	1.5 - 13 mm
Weight	0.9 kg
Battery capacity	3 Ah
Motor design	Brushless motor
maximum vibration to EN	<2,5 m/s ²
Speed range 2nd speed	0 - 1900 min ⁻¹
maximum torque hard	45 Nm
Type of product	Drill/driver
USP1	18V, 4-pole DC motor
USP2	Quick-change chuck clamping range 1.5-13, with 2 batteries, in L-Boxx