

Straight die grinder, Type: GGS30LS



Order data

Order number	077265 GGS30LS
GTIN	4053423237399
Item class	03C

Description

Version:

Handy compact straight die grinder for versatile grinding operations.

- **Constant-speed electronics maintain constant speed even at high loads.**
- **New clamping system for zero-play fixing of the grinding points for precise working.**
- **Soft start and Kick-Back stop: If the machine senses a jam, it switches off immediately.**
- **Switch-off carbon brushes for high protection of the motor.**
- **Long working life thanks to direct cooling and double sealed ball bearings.**
- **6-speed pre-selection to cater for different materials.**

Ideal for demanding metalwork and for grinding stone, even in confined spaces.

Supplied with:

Supplied with 6 mm collet, 2x AF 19 tightening wrenches.

Technical description

Weight	1.7 kg
Manufacturer's designation	GGG 30 LS
maximum collet \varnothing	6 mm
Mains frequency	50 Hz
electronic speed pre-selection	yes
maximum vibration to EN	3 m/s ²
Speed range	7000 - 33000 min ⁻¹

Nominal voltage	230 V
Power consumption	750 W
Power supply	Mains-powered
Type of product	Straight die grinder