



Electronic light metal spirit level, Length: 800



Order data

Order number	467545 800
GTIN	4007368050032
Item class	46M

Description

Version:

Electronically measures the angle and displays it digitally. The measuring computer can be calibrated both horizontally and vertically in mere seconds. Can also be used conventionally thanks to one horizontal and one vertical level. Very long operating time due to large battery capacity. Robust, powder-coated 4-chamber profile with 2 milled measuring faces.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Including battery No. 081551 6LR61, in a sturdy, transparent plastic screw tube.

Technical description

Error limit of electronics module	0.05 (0°; 90°); 0.2 (1°-89°) degrees
Power supply	Battery-powered
IP Index of Protection	IP 65
Length	800 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081551 6LR61
Error limit in normal position and for measurement reversal	0.5 mm/m
Measurement technology	digital
Calibration	H2

Type of product

Spirit level